



GreenSpace Surface Mount

SM303C P20 950 PSU NB

GreenSpace Surface Mount, 18 W, 22 W, 2040 lm, 5000 K, Frosted, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance
Light Technical	
Luminous Flux	2,040 lm
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	102 lm/W
Color rendering index (CRI)	>90
Light source color	White
Operating and Electrical	
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	18 22 W

Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class II
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Acrylate
Housing Color	White
Optical cover finish	Frosted
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]

GreenSpace Surface Mount

Optical cover type	Acrylate
Net Weight (Piece)	1.390 kg

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	SM303C P20 950 PSU NB
--------------------	-----------------------

Full product name	SM303C P20 950 PSU NB
Full product code	872016953201499
Order code	911401508422
Material Nr. (12NC)	911401508422
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169532014
Numerator - Packs per outer box	8
EAN/UPC - Case	8720169543508

Dimensional drawing

