



GreenPerform Panel RC099V G3

RC099V G3 LED71/850 PSU W60L120

GreenPerform Panel RC099V G3, 135 lm/W, 850 neutral white

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600, 300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

Product data

General Information			
Light source engine type	LED	Number of products on MCB of 16 A type B	17
Service tag	Yes	Protection class IEC	Safety class II
Value ladder	Performance		
Light Technical		Controls and Dimming	
Luminous Flux	6,800 lm	Dimmable	No
Correlated Color Temperature (Nom)	5000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	135 lm/W		
Color rendering index (CRI)	>80	Mechanical and Housing	
Light source color	850 neutral white	Housing Material	Metal
		Optical cover material	Polystyrene
Operating and Electrical		Housing Color	White RAL 9003
Input Voltage	220-240 V	Optical cover finish	Opal
Line Frequency	50 or 60 Hz	Ingress protection code	IP20 [Finger-protected]
Power Consumption	50.4 W	Mech. impact protection code	IK03 [0.3 J]
Power Factor (Fraction)	0.9	Optical cover type	Opal
		Net Weight (Piece)	3.400 kg

GreenPerform Panel RC099V G3

Approval and Application	
CE mark	Yes
Ambient temperature range	-20 °C to 45 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	RC099V G3 LED71/850 PSU W60L120

Full product name	RC099V G3 LED71/850 PSU W60L120
Order code	911401509243
Material Nr. (12NC)	911401509243
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

