



GreenPerform Panel RC099V G3

RC099V G3 LED71/840 PSU W60L120

GreenPerform Panel RC099V G3, 135 lm/W, 840 neutral white

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600, 300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

Product data

General Information	
Light source engine type	LED
Service tag	Yes
Value ladder	Performance

Light Technical	
Luminous Flux	6,800 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	135 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	50.4 W
Power Factor (Fraction)	0.9

Number of products on MCB of 16 A type B	17
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Metal
Optical cover material	Polystyrene
Housing Color	White RAL 9003
Optical cover finish	Opal
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Opal
Net Weight (Piece)	3.400 kg

GreenPerform Panel RC099V G3

Approval and Application

CE mark	Yes
Ambient temperature range	-20 °C to 45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Product Data

Order product name	RC099V G3 LED71/840 PSU W60L120
--------------------	---------------------------------

Full product name	RC099V G3 LED71/840 PSU W60L120
Order code	911401509343
Material Nr. (12NC)	911401509343
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

