



# GreenSpace Flex Luna

## RS378B P12 930 PSU-E WB M55 WP PRO

GreenSpace Flex Luna, 12.6 W, 930 warm white, IP20/54 |  
Finger-protected; dust accumulation-protected, splash-proof

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

### Product data

| General Information                         |                |
|---------------------------------------------|----------------|
| Light source engine type                    | LED            |
| Value ladder                                | Performance    |
| Light Technical                             |                |
| Luminous Flux                               | 1,450 lm       |
| Correlated Color Temperature (Nom)          | 3000 K         |
| Luminous Efficacy (rated) (Nom)             | 115 lm/W       |
| Color rendering index (CRI)                 | 92             |
| Light source color                          | 930 warm white |
| Unified glare rating CEN                    | 16             |
| Operating and Electrical                    |                |
| Input Voltage                               | 220 to 240 V   |
| Line Frequency                              | 50 or 60 Hz    |
| Power Consumption                           | 12.6 W         |
| Power Factor (Fraction)                     | 0.9            |
| Number of products on MCB of 16 A type B 52 |                |

| Protection class IEC         | Safety class II                                                       |
|------------------------------|-----------------------------------------------------------------------|
| Controls and Dimming         |                                                                       |
| Dimmable                     | -                                                                     |
| Control interface            | -                                                                     |
| Mechanical and Housing       |                                                                       |
| Housing Material             | Aluminum Alloy                                                        |
| Optical cover material       | Polycarbonate                                                         |
| Housing Color                | Black                                                                 |
| Optical cover finish         | Structured optic                                                      |
| Ingress protection code      | IP20/54 [Finger-protected; dust accumulation-protected, splash-proof] |
| Mech. impact protection code | IK03 [0.35 J reinforced]                                              |
| Optical cover type           | Lens                                                                  |
| Net Weight (Piece)           | 0.290 kg                                                              |

## GreenSpace Flex Luna

### Approval and Application

|                           |               |
|---------------------------|---------------|
| CE mark                   | Yes           |
| Ambient temperature range | -20 to +45 °C |

### Initial Performance (IEC Compliant)

|                             |             |
|-----------------------------|-------------|
| Luminous flux tolerance     | -10% / +10% |
| Power consumption tolerance | +/-10%      |

### Product Data

|                    |                                    |
|--------------------|------------------------------------|
| Order product name | RS378B P12 930 PSU-E WB M55 WP PRO |
|--------------------|------------------------------------|

|                                 |                                    |
|---------------------------------|------------------------------------|
| Full product name               | RS378B P12 930 PSU-E WB M55 WP PRO |
| Order code                      | 911401509846                       |
| Material Nr. (12NC)             | 911401509846                       |
| Numerator - Quantity Per Pack   | 1                                  |
| Numerator - Packs per outer box | 48                                 |

### Dimensional drawing

