



# GreenPerform Panel RC099V G3

## RC099V G3 LED50/840 PSU W60L60

GreenPerform Panel RC099V G3, 120 lm/W, 840 neutral white

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600, 300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

### Product data

General Information	
Light source engine type	LED
Service tag	Yes
Value ladder	Performance

  

Light Technical	
Luminous Flux	4,800 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	120 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white

  

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	40 W
Power Factor (Fraction)	0.9

  

Number of products on MCB of 16 A type B	17
Protection class IEC	Safety class II

  

Controls and Dimming	
Dimmable	No
Control interface	-

  

Mechanical and Housing	
Housing Material	Metal
Optical cover material	Polystyrene
Housing Color	White RAL 9003
Optical cover finish	Opal
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Opal
Net Weight (Piece)	1.800 kg

# GreenPerform Panel RC099V G3

## Approval and Application

CE mark	Yes
Ambient temperature range	-20 °C to 45 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

## Product Data

Order product name	RC099V G3 LED50/840 PSU W60L60
--------------------	--------------------------------

Full product name	RC099V G3 LED50/840 PSU W60L60
Order code	911401509943
Material Nr. (12NC)	911401509943
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4

