PHILIPS

Lighting

GreenSpace Grid

GD309B 3*P20 930 PSU-E WB

GreenSpace Grid, 54 W, 66 W, 930 warm white, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Grid product family offers a complete range of options with comprehensive control availability, optical solutions and powerful lumen outputs, meanwhile ensures the product reliability and quality within compact luminaire body.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance

Light Technical	
Luminous Flux	6,070 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	101 lm/W
Color rendering index (CRI)	>90
Light source color	930 warm white

Operating and Electrical	
Input Voltage	200 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	54 66 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Acrylate
Housing Color	White
Optical cover finish	Frosted
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Acrylate
Net Weight (Piece)	2.030 kg

GreenSpace Grid

Approval and Application	
CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	GD309B 3*P20 930 PSU-E WB

Full product name	GD309B 3*P20 930 PSU-E WB
Full product code	872016952965699
Order code	911401511412
Material Nr. (12NC)	911401511412
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169529656
Numerator - Packs per outer box	4
EAN/UPC - Case	8720169541146

Dimensional drawing



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.