



GreenSpace linear accent

RS386B S10 P20 935 PSU-E NB WH

GreenSpace linear accent, 18 W, 1150 lm, 3500 K

GreenSpace Linear accent is a comprehensive product offer with multiple modules available. By means of its modular design, it offers flexible lumen output for different indoor applications, such as office, retail and hospitality. This family provides both surface mounted and recessed installations with high CRI90 and 3 different beam angles to perfectly fit the light requirement of the indoor applications. Dali and 1-10V control interfaces give the way for future system connections as well.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance

Light Technical	
Luminous Flux	1,150 lm
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	65 lm/W
Color rendering index (CRI)	>90
Light source color	935 warm white

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	18 W
Power Factor (Fraction)	0.9

Number of products on MCB of 16 A type B 25	
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Polycarbonate
Housing Color	Black and white
Optical cover finish	Matte
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	Polycarbonate cover and gloss high-reflective optic

GreenSpace linear accent

Net Weight (Piece)	0.450 kg
--------------------	----------

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	RS386B S10 P20 935 PSU-E NB WH
--------------------	--------------------------------

Full product name	RS386B S10 P20 935 PSU-E NB WH
Full product code	692382866277699
Order code	66277699
Material Nr. (12NC)	911401511902
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828662776
Numerator - Packs per outer box	10
EAN/UPC - Case	6923828664558

Dimensional drawing

