



GreenPerform Canopy Mini500 G4

BGP500 G4 LED85/CW PSU A-WB

GreenPerform Canopy Mini500 G4, 53 W, 8496 lm, 6500 K

The Philips GreenPerform Canopy Mini500 Gen4 lives up to the GreenPerform family's enviable reputation for reliable performance. Not only does this next-generation, energy-saving LED deliver leading system efficacy and extended long-term quality, it also offers a versatile selection of optics, connectivity, controls and installation options. So you can create the ideal lighting conditions for any space, at any time. The GreenPerform Canopy portfolio also includes a series that is ideal for canopy lighting in food applications. For professionals who demand high-performance, connected lighting for their lighting installations, this robust, optimized, and versatile family of LED canopy luminaires is the perfect choice for both indoor and outdoor canopy applications.

Product data

| General Information | | Operating and Electrical | |
|------------------------------------|-------------------|--|----------------|
| Light source engine type | LED | Input Voltage | 220-240 V |
| Service tag | Yes | Line Frequency | 50 to 60 Hz |
| Value ladder | Performance | Inrush current | 35.4 A |
| Light Technical | | Power Consumption | 53 W |
| Luminous Flux | 8,496 lm | Power Factor (Fraction) | 0.9 |
| Correlated Color Temperature (Nom) | 6500 K | Number of products on MCB of 16 A type B 8 | |
| Luminous Efficacy (rated) (Nom) | 160 lm/W | Protection class IEC | Safety class I |
| Color rendering index (CRI) | >80 | Controls and Dimming | |
| Light source color | 865 cool daylight | Dimmable | No |

GreenPerform Canopy Mini500 G4

| | |
|-------------------------------------|---|
| Control interface | - |
| Mechanical and Housing | |
| Housing Material | Aluminium die-cast ADC1 - alloy grade (EN AC-47100) |
| Optical cover material | Tempered glass |
| Housing Color | White |
| Optical cover finish | Clear |
| Overall length | 335 mm |
| Overall width | 335 mm |
| Overall height | 200 mm |
| Dimensions (Height x Width x Depth) | 200 x 335 x 335 mm |
| Ingress protection code | IP65 [Dust penetration-protected, jet-proof] |
| Mech. impact protection code | IK07 [2 J reinforced] |
| Optical cover type | Clear glass |
| Net Weight (Piece) | 5.990 kg |
| Approval and Application | |
| Flammability mark | - |

| | |
|--|-----------------------------|
| CE mark | Yes |
| Ambient temperature range | -40 to +50 °C |
| Initial Performance (IEC Compliant) | |
| Luminous flux tolerance | +/-10% |
| Power consumption tolerance | +/-10% |
| Product Data | |
| Order product name | BGP500 G4 LED85/CW PSU A-WB |
| Full product name | BGP500 G4 LED85/CW PSU A-WB |
| Full product code | 872016954708700 |
| Order code | 911401512442 |
| Material Nr. (12NC) | 911401512442 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8720169547087 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8720169547087 |

Dimensional drawing

