



# GreenPerform Troffer

## RC100B LED37S 840 W30L120 PSU G3

GreenPerform Troffer, 116 lm/W, 840 neutral white

GreenPerform troffer improves the compact design of the last generation with performance improvement and more variants for different markets. Integrating with all available system: POE, InterAct office wireless, InterAct Office Pro, ActiLume controller, GreenPerform troffer offers additional energy saving and connected features.

### Product data

General Information	
Light source replaceable	No
Number of gear units	1 unit
Driver included	Yes
Light source engine type	LED
Service tag	Yes
Value ladder	Performance
Warranty period	3 years
Light Technical	
Luminous Flux	3,700 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	116 lm/W
Color rendering index (CRI)	80
Light source color	840 neutral white
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	3 A

Inrush time	62 ms
Power Consumption	32 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	24
Suitable for random switching	No
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	No
Control interface	-
Constant light output	No
Mechanical and Housing	
Housing Material	Metal
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Steel
Housing Color	White
Optical cover finish	Ribbed
Overall length	1,197 mm

## GreenPerform Troffer

Overall width	297 mm
Overall height	46 mm
Dimensions (Height x Width x Depth)	46 x 297 x 1197 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Variable linear-lens array in polycarbonate cover
Net Weight (Piece)	2.799 kg

### Approval and Application

Glow-wire test	Temperature 600 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
Ambient temperature range	-20 to +40 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Initial chromaticity	SDCM<4
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Median useful life L70B50	50,000 hour(s)
---------------------------	----------------

### Product Data

Order product name	RC100B LED37S 840 W30L120 PSU G3
Full product name	RC100B LED37S 840 W30L120 PSU G3
Full product code	872016972781699
Order code	911401513351
Material Nr. (12NC)	911401513351
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169727816
Numerator - Packs per outer box	2
EAN/UPC - Case	8720169727816

### Dimensional drawing

