



GreenSpace Flex Luna

RS378B P12 930 PSD-E WB M70 PRO

GreenSpace Flex Luna, 12.8 W, 930 warm white, DALI, IP20 | Finger-protected

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

Product data

General Information		Protection class IEC	
Light source engine type	LED		Safety class II
Value ladder	Performance		
Light Technical		Controls and Dimming	
Luminous Flux	1,655 lm	Dimmable	DALI
Correlated Color Temperature (Nom)	3000 K	Control interface	DALI
Luminous Efficacy (rated) (Nom)	129 lm/W	Mechanical and Housing	
Color rendering index (CRI)	92	Housing Material	Aluminum Alloy
Light source color	930 warm white	Optical cover material	Polycarbonate
Unified glare rating CEN	16	Housing Color	Black
Operating and Electrical		Optical cover finish	Structured optic
Input Voltage	220 to 240 V	Ingress protection code	IP20 [Finger-protected]
Line Frequency	50 or 60 Hz	Mech. impact protection code	IK03 [0.35 J reinforced]
Power Consumption	12.8 W	Optical cover type	Lens
Power Factor (Fraction)	0.9	Net Weight (Piece)	0.428 kg
Number of products on MCB of 16 A type B	85	Approval and Application	
		CE mark	Yes

GreenSpace Flex Luna

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Product Data

Order product name	RS378B P12 930 PSD-E WB M70 PRO
--------------------	---------------------------------

Full product name	RS378B P12 930 PSD-E WB M70 PRO
Order code	911401514446
Material Nr. (12NC)	911401514446
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	18

Dimensional drawing

