



GreenSpace linear accent

SM386C S5 P10 935 PSU WB WH

GreenSpace linear accent, 9 W, 575 lm, 3500 K

GreenSpace Linear accent is a comprehensive product offer with multiple modules available. By means of its modular design, it offers flexible lumen output for different indoor applications, such as office, retail and hospitality. This family provides both surface mounted and recessed installations with high CRI90 and 3 different beam angles to perfectly fit the light requirement of the indoor applications. Dali and 1-10V control interfaces give the way for future system connections as well.

Product data

General Information		Number of products on MCB of 16 A type B 36	
Light source engine type	LED	Protection class IEC	Safety class II
Value ladder	Performance		
Light Technical		Controls and Dimming	
Luminous Flux	575 lm	Dimmable	No
Correlated Color Temperature (Nom)	3500 K	Control interface	-
Luminous Efficacy (rated) (Nom)	64 lm/W		
Color rendering index (CRI)	>90	Mechanical and Housing	
Light source color	935 warm white	Housing Material	Aluminum Alloy
Operating and Electrical		Optical cover material	Polycarbonate
Input Voltage	220 to 240 V	Housing Color	Black and white
Line Frequency	50 or 60 Hz	Optical cover finish	Matte
Power Consumption	9 W	Ingress protection code	IP20 [Finger-protected]
Power Factor (Fraction)	0.9	Mech. impact protection code	IK02 [0.2 J standard]
		Optical cover type	Polycarbonate cover and gloss high-reflective optic

GreenSpace linear accent

Net Weight (Piece)	0.340 kg
--------------------	----------

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	SM386C S5 P10 935 PSU WB WH
--------------------	-----------------------------

Full product name	SM386C S5 P10 935 PSU WB WH
Full product code	692382866321699
Order code	911401516302
Material Nr. (12NC)	911401516302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828663216
Numerator - Packs per outer box	12
EAN/UPC - Case	6923828664992

Dimensional drawing

