



GreenSpace Flex Luna

RS378B P20 940 PSD-E WB M70 PRO

GreenSpace Flex Luna, 20.5 W, 940 neutral white, DALI, IP20 | Finger-protected

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

Product data

| General Information | | Protection class IEC | |
|--|-------------------|------------------------------|--------------------------|
| Light source engine type | LED | Safety class II | |
| Value ladder | Performance | Controls and Dimming | |
| Light Technical | | Dimmable | DALI |
| Luminous Flux | 2,605 lm | Control interface | DALI |
| Correlated Color Temperature (Nom) | 4000 K | Mechanical and Housing | |
| Luminous Efficacy (rated) (Nom) | 127 lm/W | Housing Material | Aluminum Alloy |
| Color rendering index (CRI) | 92 | Optical cover material | Polycarbonate |
| Light source color | 940 neutral white | Housing Color | Black |
| Unified glare rating CEN | 16 | Optical cover finish | Structured optic |
| Operating and Electrical | | Ingress protection code | IP20 [Finger-protected] |
| Input Voltage | 220 to 240 V | Mech. impact protection code | IK03 [0.35 J reinforced] |
| Line Frequency | 50 or 60 Hz | Optical cover type | Lens |
| Power Consumption | 20.5 W | Net Weight (Piece) | 0.467 kg |
| Power Factor (Fraction) | 0.9 | Approval and Application | |
| Number of products on MCB of 16 A type B | 47 | CE mark | Yes |

GreenSpace Flex Luna

| | |
|---------------------------|---------------|
| Ambient temperature range | -20 to +45 °C |
|---------------------------|---------------|

Initial Performance (IEC Compliant)

| | |
|-------------------------|-------------|
| Luminous flux tolerance | -10% / +10% |
|-------------------------|-------------|

| | |
|-----------------------------|--------|
| Power consumption tolerance | +/-10% |
|-----------------------------|--------|

Product Data

| | |
|--------------------|---------------------------------|
| Order product name | RS378B P20 940 PSD-E WB M70 PRO |
|--------------------|---------------------------------|

| | |
|-------------------|---------------------------------|
| Full product name | RS378B P20 940 PSD-E WB M70 PRO |
|-------------------|---------------------------------|

| | |
|------------|--------------|
| Order code | 911401516346 |
|------------|--------------|

| | |
|---------------------|--------------|
| Material Nr. (12NC) | 911401516346 |
|---------------------|--------------|

| | |
|-------------------------------|---|
| Numerator - Quantity Per Pack | 1 |
|-------------------------------|---|

| | |
|---------------------------------|----|
| Numerator - Packs per outer box | 18 |
|---------------------------------|----|

Dimensional drawing

