



GreenSpace linear accent

SM386C S10 P20 940 PSU WB WH

GreenSpace linear accent, 18 W, 1150 lm, 4000 K

GreenSpace Linear accent is a comprehensive product offer with multiple modules available. By means of its modular design, it offers flexible lumen output for different indoor applications, such as office, retail and hospitality. This family provides both surface mounted and recessed installations with high CRI90 and 3 different beam angles to perfectly fit the light requirement of the indoor applications. Dali and 1-10V control interfaces give the way for future system connections as well.

Product data

| General Information | | Number of products on MCB of 16 A type B 25 | |
|------------------------------------|-------------------|---|---|
| Light source engine type | LED | Protection class IEC | Safety class II |
| Value ladder | Performance | | |
| Light Technical | | Controls and Dimming | |
| Luminous Flux | 1,150 lm | Dimmable | No |
| Correlated Color Temperature (Nom) | 4000 K | Control interface | - |
| Luminous Efficacy (rated) (Nom) | 65 lm/W | Mechanical and Housing | |
| Color rendering index (CRI) | >90 | Housing Material | Aluminum Alloy |
| Light source color | 940 neutral white | Optical cover material | Polycarbonate |
| Operating and Electrical | | Housing Color | Black and white |
| Input Voltage | 220 to 240 V | Optical cover finish | Matte |
| Line Frequency | 50 or 60 Hz | Ingress protection code | IP20 [Finger-protected] |
| Power Consumption | 18 W | Mech. impact protection code | IK02 [0.2 J standard] |
| Power Factor (Fraction) | 0.9 | Optical cover type | Polycarbonate cover and gloss high-reflective optic |

GreenSpace linear accent

| | |
|--------------------|----------|
| Net Weight (Piece) | 0.510 kg |
|--------------------|----------|

Approval and Application

| | |
|---------------------------|---------------|
| CE mark | No |
| Ambient temperature range | -20 to +40 °C |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|--------|
| Luminous flux tolerance | +/-10% |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|--------------------|------------------------------|
| Order product name | SM386C S10 P20 940 PSU WB WH |
|--------------------|------------------------------|

| | |
|---------------------------------|------------------------------|
| Full product name | SM386C S10 P20 940 PSU WB WH |
| Full product code | 692382866336099 |
| Order code | 911401517802 |
| Material Nr. (12NC) | 911401517802 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 6923828663360 |
| Numerator - Packs per outer box | 10 |
| EAN/UPC - Case | 6923828665142 |

Dimensional drawing

