



GreenSpace linear accent

SM386C S10 P20 940 PSU WB WH

GreenSpace linear accent, 18 W, 940 neutral white, IP20 | Finger-protected

GreenSpace Linear accent is a comprehensive product offer with multiple modules available. By means of its modular design, it offers flexible lumen output for different indoor applications, such as office, retail and hospitality. This family provides both surface mounted and recessed installations with high CRI90 and 3 different beam angles to perfectly fit the light requirement of the indoor applications. Dali and 1-10V control interfaces give the way for future system connections as well.

Product data

General Information		Power Factor (Fraction)		0.9
Light source engine type	LED	Number of products on MCB of 16 A type B		25
Value ladder	Performance	Protection class IEC		Safety class II
Light Technical		Controls and Dimming		
Luminous Flux	1,150 lm	Dimmable	No	
Correlated Color Temperature (Nom)	4000 K	Control interface		-
Luminous Efficacy (rated) (Nom)	65 lm/W	Mechanical and Housing		
Color rendering index (CRI)	>90	Housing Material	Aluminum Alloy	
Light source color	940 neutral white	Optical cover material	Polycarbonate	
Operating and Electrical		Housing Color	Black and white	
Input Voltage	220 to 240 V	Optical cover finish	Matte	
Line Frequency	50 or 60 Hz	Ingress protection code	IP20 [Finger-protected]	
Power Consumption	18 W	Mech. impact protection code	IK02 [0.2 J standard]	

GreenSpace linear accent

Optical cover type	Polycarbonate cover and gloss high-reflective optic
Net Weight (Piece)	0.510 kg
Approval and Application	
CE mark	No
Ambient temperature range	-20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	SM386C S10 P20 940 PSU WB WH
Full product name	SM386C S10 P20 940 PSU WB WH
Full product code	692382866336099
Order code	911401517802
Material Nr. (12NC)	911401517802
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828663360
Numerator - Packs per outer box	10
EAN/UPC - Case	6923828665142

Dimensional drawing

