



# Truefashion Projector GCGM

## GD700B LED10 830 PSU MB BK

Truefashion Projector GCGM, 8.2 W, 942 lm, 3000 K

Truefashion Projector is offering a retail segment with attractive outlook design, excellent quality of light & dedicated light recipe as well as system connectivity, to create a comfortable ambiance and impressive shopping experience to stimulate the store sales for retail customers.

### Warnings and Safety

- 3 years

### Product data

General Information		Power Consumption	
Light source engine type	LED	Power Consumption	8.2 W
Service tag	Yes	Power Factor (Fraction)	0.91
Value ladder	Specification	Number of products on MCB of 16 A type B	1
		Protection class IEC	Safety class II
Light Technical		Controls and Dimming	
Luminous Flux	942 lm	Dimmable	No
Correlated Color Temperature (Nom)	3000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	115 lm/W		
Color rendering index (CRI)	>80	Mechanical and Housing	
Light source color	830 warm white	Housing Material	Aluminum
		Optical cover material	Polymethyl methacrylate
Operating and Electrical		Housing Color	Black
Input Voltage	220 to 240 V	Optical cover finish	-
Line Frequency	50 or 60 Hz	Overall length	100 mm

# Truefashion Projector GCGM

Overall width	100 mm
Overall height	75 mm
Dimensions (Height x Width x Depth)	75 x 100 x 100 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	-
Optical cover type	Lens
Net Weight (Piece)	0.350 kg

## Approval and Application

CE mark	Yes
Ambient temperature range	-15 to +35 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

## Product Data

Order product name	GD700B LED10 830 PSU MB BK
Full product name	GD700B LED10 830 PSU MB BK
Full product code	911401518471
Order code	01518471
Material Nr. (12NC)	911401518471
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing

