



Truefashion Projector GCGM

GD700B LED20 930PW PSU MB BK

Truefashion Projector GCGM, 21.2 W, 930 warm white, IP20 |
Finger-protected

Truefashion Projector is offering a retail segment with attractive outlook design, excellent quality of light & dedicated light recipe as well as system connectivity, to create a comfortable ambiance and impressive shopping experience to stimulate the store sales for retail customers.

Warnings and Safety

- 3 years

Product data

General Information		Line Frequency	
Light source engine type	LED		50 or 60 Hz
Service tag	Yes	Power Consumption	21.2 W
Value ladder	Specification	Power Factor (Fraction)	0.97
Light Technical		Number of products on MCB of 16 A type B	1
Luminous Flux	1,685 lm	Protection class IEC	Safety class II
Correlated Color Temperature (Nom)	3000 K	Controls and Dimming	
Luminous Efficacy (rated) (Nom)	79 lm/W	Dimmable	No
Color rendering index (CRI)	>90	Control interface	-
Light source color	930 warm white	Mechanical and Housing	
Operating and Electrical		Housing Material	Aluminum
Input Voltage	220 to 240 V	Optical cover material	Polymethyl methacrylate
		Housing Color	Black

Truefashion Projector GCGM

Optical cover finish	-
Overall length	100 mm
Overall width	100 mm
Overall height	75 mm
Dimensions (Height x Width x Depth)	75 x 100 x 100 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	-
Optical cover type	Lens
Net Weight (Piece)	0.350 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-15 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data

Order product name	GD700B LED20 930PW PSU MB BK
Full product name	GD700B LED20 930PW PSU MB BK
Full product code	872016973101100
Order code	911401518671
Material Nr. (12NC)	911401518671
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169731011
Numerator - Packs per outer box	1
EAN/UPC - Case	8720169731011

Dimensional drawing

