



Truefashion Projector GCGM

GD700B 2XLED20 930PW PSU MB WH

Truefashion Projector GCGM, 42.4 W, 3369 lm, 3000 K

Truefashion Projector is offering a retail segment with attractive outlook design, excellent quality of light & dedicated light recipe as well as system connectivity, to create a comfortable ambiance and impressive shopping experience to stimulate the store sales for retail customers.

Warnings and Safety

- 3 years

Product data

General Information		Power Consumption	
Light source engine type	LED	Power Consumption	42.4 W
Service tag	Yes	Power Factor (Fraction)	0.97
Value ladder	Specification	Number of products on MCB of 16 A type B	1
		Protection class IEC	Safety class II
Light Technical		Controls and Dimming	
Luminous Flux	3,369 lm	Dimmable	No
Correlated Color Temperature (Nom)	3000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	79 lm/W		
Color rendering index (CRI)	>90	Mechanical and Housing	
Light source color	930 warm white	Housing Material	Aluminum
Operating and Electrical		Optical cover material	Polymethyl methacrylate
Input Voltage	220 to 240 V	Housing Color	White RAL 9003
Line Frequency	50 or 60 Hz	Optical cover finish	-
		Overall length	217 mm

Truefashion Projector GCGM

Overall width	115 mm
Overall height	75 mm
Dimensions (Height x Width x Depth)	75 x 115 x 217 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	-
Optical cover type	Lens
Net Weight (Piece)	0.750 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-15 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data

Order product name	GD700B 2XLED20 930PW PSU MB WH
Full product name	GD700B 2XLED20 930PW PSU MB WH
Full product code	911401518971
Order code	911401518971
Material Nr. (12NC)	911401518971
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

