



# GreenSpace Flex Luna

## RS378B P9 PSD-TNW NB M55 PRO

GreenSpace Flex Luna, 9 W, Tunable white, DALI, IP20 | Finger-protected

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

### Product data

General Information		Protection class IEC	
Light source engine type	LED		Safety class II
Value ladder	Performance		
Light Technical		Controls and Dimming	
Luminous Flux	650 lm	Dimmable	DALI
Correlated Color Temperature (Nom)	Tunable White	Control interface	DALI
Luminous Efficacy (rated) (Nom)	72 lm/W		
Color rendering index (CRI)	90	Mechanical and Housing	
Light source color	Tunable white	Housing Material	Aluminum Alloy
Unified glare rating CEN	16	Optical cover material	Polycarbonate
Operating and Electrical		Housing Color	Black
Input Voltage	220 to 240 V	Optical cover finish	Structured optic
Line Frequency	50 or 60 Hz	Ingress protection code	IP20 [Finger-protected]
Power Consumption	9 W	Mech. impact protection code	IK03 [0.35 J reinforced]
Power Factor (Fraction)	0.9	Optical cover type	Lens
Number of products on MCB of 16 A type B	70	Net Weight (Piece)	0.240 kg
		Approval and Application	
		CE mark	No

## GreenSpace Flex Luna

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

### Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

### Product Data

Order product name	RS378B P9 PSD-TNW NB M55 PRO
--------------------	------------------------------

Full product name	RS378B P9 PSD-TNW NB M55 PRO
-------------------	------------------------------

Order code	911401519246
------------	--------------

Material Nr. (12NC)	911401519246
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	36
---------------------------------	----

## Dimensional drawing

