



# GreenPerform Panel RC099V G3

## RC099V G3 LED50/950 PSD W60L120 OC CAUHE

GreenPerform Panel RC099V G3, 130 lm/W, 950, DALI

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600, 300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

### Product data

General Information	
Light source engine type	LED
Service tag	Yes
Value ladder	Performance

  

Light Technical	
Luminous Flux	5,000 lm
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	130 lm/W
Color rendering index (CRI)	>90
Light source color	950

  

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	38.5 W
Power Factor (Fraction)	0.9

  

Number of products on MCB of 16 A type B 17	
Protection class IEC	Safety class II

  

Controls and Dimming	
Dimmable	DALI
Control interface	DALI

  

Mechanical and Housing	
Housing Material	Metal
Optical cover material	Polystyrene
Housing Color	White RAL 9003
Optical cover finish	Opal
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Opal
Net Weight (Piece)	3.390 kg

# GreenPerform Panel RC099V G3

## Approval and Application

CE mark	Yes
Ambient temperature range	-20 °C to 45 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

## Product Data

Order product name	RC099V G3 LED50/950 PSD W60L120 OC CAUHE
--------------------	---

Full product name	RC099V G3 LED50/950 PSD W60L120 OC CAUHE
Order code	911401519743
Material Nr. (12NC)	911401519743
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2

