



# Truefashion Projector GCGM

## RS700B LED20 940PW PSU MB WH

Truefashion Projector GCGM, 21.2 W, 1829 lm, 4000 K

Truefashion Projector is offering a retail segment with attractive outlook design, excellent quality of light & dedicated light recipe as well as system connectivity, to create a comfortable ambiance and impressive shopping experience to stimulate the store sales for retail customers.

### Warnings and Safety

- 3 years

### Product data

General Information		Power Consumption	
Light source engine type	LED	Power Consumption	21.2 W
Service tag	Yes	Power Factor (Fraction)	0.97
Value ladder	Specification	Number of products on MCB of 16 A type B	1
		Protection class IEC	Safety class II
Light Technical		Controls and Dimming	
Luminous Flux	1,829 lm	Dimmable	No
Correlated Color Temperature (Nom)	4000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	86 lm/W		
Color rendering index (CRI)	>90	Mechanical and Housing	
Light source color	940 neutral white	Housing Material	Aluminum
		Optical cover material	Polymethyl methacrylate
Operating and Electrical		Housing Color	White RAL 9003
Input Voltage	220 to 240 V	Optical cover finish	-
Line Frequency	50 or 60 Hz	Overall height	70 mm

# Truefashion Projector GCGM

Overall diameter	96 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	-
Optical cover type	Lens
Net Weight (Piece)	0.330 kg

## Approval and Application

CE mark	Yes
Ambient temperature range	-15 to +35 °C

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Power consumption tolerance	+/-10%
-----------------------------	--------

## Product Data

Order product name	RS700B LED20 940PW PSU MB WH
Full product name	RS700B LED20 940PW PSU MB WH
Full product code	911401520071
Order code	911401520071
Material Nr. (12NC)	911401520071
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

## Dimensional drawing

