



GreenPerform Panel RC099V G3

RC099V G3 LED29/950 PSD W30L120 OC CAUHE

GreenPerform Panel RC099V G3, 125 lm/W, 950, DALI

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600, 300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

Product data

General Information	
Light source engine type	LED
Service tag	Yes
Value ladder	Performance

Light Technical	
Luminous Flux	2.900 lm
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	125 lm/W
Color rendering index (CRI)	>90
Light source color	950

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	23.2 W
Power Factor (Fraction)	0.9

Number of products on MCB of 16 A type B 17	
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	DALI
Control interface	DALI

Mechanical and Housing	
Housing Material	Metal
Optical cover material	Polystyrene
Housing Color	White RAL 9003
Optical cover finish	Opal
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Opal
Net Weight (Piece)	1.940 kg

GreenPerform Panel RC099V G3

Approval and Application

CE mark	Yes
Ambient temperature range	-20 °C to 45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Product Data

Order product name	RC099V G3 LED29/950 PSD W30L120 OC CAUHE
--------------------	---

Full product name	RC099V G3 LED29/950 PSD W30L120 OC CAUHE
Order code	911401520343
Material Nr. (12NC)	911401520343
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4

