



GreenSpace linear accent

RS386B S5 P10 940 PSD-E WB BK

GreenSpace linear accent, 10 W, 940 neutral white, DALI, IP20 | Finger-protected

GreenSpace Linear accent is a comprehensive product offer with multiple modules available. By means of its modular design, it offers flexible lumen output for different indoor applications, such as office, retail and hospitality. This family provides both surface mounted and recessed installations with high CRI90 and 3 different beam angles to perfectly fit the light requirement of the indoor applications. Dali and 1-10V control interfaces give the way for future system connections as well.

Product data

General Information		Power Factor (Fraction)		0.9
Light source engine type	LED	Number of products on MCB of 16 A type B		71
Value ladder	Performance	Protection class IEC		Safety class II
Light Technical		Controls and Dimming		
Luminous Flux	575 lm	Dimmable	Yes	
Correlated Color Temperature (Nom)	4000 K	Control interface	DALI	
Luminous Efficacy (rated) (Nom)	64 lm/W	Mechanical and Housing		
Color rendering index (CRI)	>90	Housing Material	Aluminum Alloy	
Light source color	940 neutral white	Optical cover material	Polycarbonate	
Operating and Electrical		Housing Color	Black and white	
Input Voltage	220 to 240 V	Optical cover finish	Matte	
Line Frequency	50 or 60 Hz	Ingress protection code	IP20 [Finger-protected]	
Power Consumption	10 W	Mech. impact protection code	IK02 [0.2 J standard]	

GreenSpace linear accent

Optical cover type	Polycarbonate cover and gloss high-reflective optic
Net Weight (Piece)	0.290 kg
Approval and Application	
CE mark	No
Ambient temperature range	-20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	RS386B S5 P10 940 PSD-E WB BK
Full product name	RS386B S5 P10 940 PSD-E WB BK
Full product code	692382866385899
Order code	911401522702
Material Nr. (12NC)	911401522702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828663858
Numerator - Packs per outer box	18
EAN/UPC - Case	6923828665630

Dimensional drawing

