



# GreenSpace linear accent

**RS386B S10 P20 940 PSD-E WB BK**

GreenSpace linear accent, 18 W, 1150 lm, 4000 K, DALI

GreenSpace Linear accent is a comprehensive product offer with multiple modules available. By means of its modular design, it offers flexible lumen output for different indoor applications, such as office, retail and hospitality. This family provides both surface mounted and recessed installations with high CRI90 and 3 different beam angles to perfectly fit the light requirement of the indoor applications. Dali and 1-10V control interfaces give the way for future system connections as well.

## Product data

| General Information                |                   | Number of products on MCB of 16 A type B 53 |   |
|------------------------------------|-------------------|---|---|
| Light source engine type           | LED               | Protection class IEC                        | Safety class II                                     |
| Value ladder                       | Performance       |   |   |
| Light Technical                    |                   | Controls and Dimming                        |   |
| Luminous Flux                      | 1,150 lm          | Dimmable                                    | Yes   |
| Correlated Color Temperature (Nom) | 4000 K            | Control interface                           | DALI  |
| Luminous Efficacy (rated) (Nom)    | 65 lm/W           |   |   |
| Color rendering index (CRI)        | >90               | Mechanical and Housing                      |   |
| Light source color                 | 940 neutral white | Housing Material                            | Aluminum Alloy                                      |
| Operating and Electrical           |                   | Optical cover material                      | Polycarbonate                                       |
| Input Voltage                      | 220 to 240 V      | Housing Color                               | Black and white                                     |
| Line Frequency                     | 50 or 60 Hz       | Optical cover finish                        | Matte   |
| Power Consumption                  | 18 W              | Ingress protection code                     | IP20 [Finger-protected]                             |
| Power Factor (Fraction)            | 0.9               | Mech. impact protection code                | IK02 [0.2 J standard]                               |
|                                    |                   | Optical cover type                          | Polycarbonate cover and gloss high-reflective optic |

## GreenSpace linear accent

|                    |          |
|--------------------|----------|
| Net Weight (Piece) | 0.470 kg |
|--------------------|----------|

### Approval and Application

|                           |               |
|---------------------------|---------------|
| CE mark                   | No            |
| Ambient temperature range | -20 to +40 °C |

### Initial Performance (IEC Compliant)

|                             |        |
|-----------------------------|--------|
| Luminous flux tolerance     | +/-10% |
| Power consumption tolerance | +/-10% |

### Product Data

|                    |                                |
|--------------------|--------------------------------|
| Order product name | RS386B S10 P20 940 PSD-E WB BK |
|--------------------|--------------------------------|

|                                 |                                |
|---------------------------------|--------------------------------|
| Full product name               | RS386B S10 P20 940 PSD-E WB BK |
| Full product code               | 692382866399599                |
| Order code                      | 911401524102                   |
| Material Nr. (12NC)             | 911401524102                   |
| Numerator - Quantity Per Pack   | 1                              |
| EAN/UPC - Product/Case          | 6923828663995                  |
| Numerator - Packs per outer box | 10                             |
| EAN/UPC - Case                  | 6923828665777                  |

## Dimensional drawing

