



GreenSpace linear accent

SM386C S5 P10 940 PSD WB BK

GreenSpace linear accent, 10 W, 575 lm, 4000 K, DALI

GreenSpace Linear accent is a comprehensive product offer with multiple modules available. By means of its modular design, it offers flexible lumen output for different indoor applications, such as office, retail and hospitality. This family provides both surface mounted and recessed installations with high CRI90 and 3 different beam angles to perfectly fit the light requirement of the indoor applications. Dali and 1-10V control interfaces give the way for future system connections as well.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance

Light Technical	
Luminous Flux	575 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	64 lm/W
Color rendering index (CRI)	>90
Light source color	940 neutral white

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	10 W
Power Factor (Fraction)	0.9

Number of products on MCB of 16 A type B 71	
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	Yes
Control interface	DALI

Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Polycarbonate
Housing Color	Black and white
Optical cover finish	Matte
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	Polycarbonate cover and gloss high-reflective optic

GreenSpace linear accent

Net Weight (Piece)	0.365 kg
Approval and Application	
CE mark	No
Ambient temperature range	-20 to +40 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	SM386C S5 P10 940 PSD WB BK
--------------------	-----------------------------

Full product name	SM386C S5 P10 940 PSD WB BK
Full product code	692382866417699
Order code	911401525502
Material Nr. (12NC)	911401525502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828664176
Numerator - Packs per outer box	12
EAN/UPC - Case	6923828665913

Dimensional drawing

