



GreenSpace linear accent

SM386C S10 P20 940 PSD WB WH

GreenSpace linear accent, 18 W, 1150 lm, 4000 K, DALI

GreenSpace Linear accent is a comprehensive product offer with multiple modules available. By means of its modular design, it offers flexible lumen output for different indoor applications, such as office, retail and hospitality. This family provides both surface mounted and recessed installations with high CRI90 and 3 different beam angles to perfectly fit the light requirement of the indoor applications. Dali and 1-10V control interfaces give the way for future system connections as well.

Product data

General Information		Number of products on MCB of 16 A type B 53	
Light source engine type	LED	Protection class IEC	Safety class II
Value ladder	Performance		
Light Technical		Controls and Dimming	
Luminous Flux	1,150 lm	Dimmable	Yes
Correlated Color Temperature (Nom)	4000 K	Control interface	DALI
Luminous Efficacy (rated) (Nom)	65 lm/W	Mechanical and Housing	
Color rendering index (CRI)	>90	Housing Material	Aluminum Alloy
Light source color	940 neutral white	Optical cover material	Polycarbonate
Operating and Electrical		Housing Color	Black and white
Input Voltage	220 to 240 V	Optical cover finish	Matte
Line Frequency	50 or 60 Hz	Ingress protection code	IP20 [Finger-protected]
Power Consumption	18 W	Mech. impact protection code	IK02 [0.2 J standard]
Power Factor (Fraction)	0.9	Optical cover type	Polycarbonate cover and gloss high-reflective optic

GreenSpace linear accent

Net Weight (Piece)	0.520 kg
--------------------	----------

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	SM386C S10 P20 940 PSD WB WH
--------------------	------------------------------

Full product name	SM386C S10 P20 940 PSD WB WH
Full product code	692382866426899
Order code	911401526202
Material Nr. (12NC)	911401526202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828664268
Numerator - Packs per outer box	10
EAN/UPC - Case	6923828665982

Dimensional drawing

