



GreenSpace Flex Luna

SM378B R P8 940 PSD-E MB D100 G-TT PRO

GreenSpace Flex Luna, 9 W, 990 lm, 4000 K, DALI, Structured optic, IP20 | Finger-protected

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

Product data

| General Information | |
|--|-------------------|
| Light source engine type | LED |
| Value ladder | Performance |
| Light Technical | |
| Luminous Flux | 990 lm |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 110 lm/W |
| Color rendering index (CRI) | 92 |
| Light source color | 940 neutral white |
| Unified glare rating CEN | 16 |
| Operating and Electrical | |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 or 60 Hz |
| Power Consumption | 9 W |
| Power Factor (Fraction) | 0.9 |
| Number of products on MCB of 16 A type B | 85 |

| Protection class IEC | Safety class II |
|------------------------------|--------------------------|
| Controls and Dimming | |
| Dimmable | DALI |
| Control interface | DALI |
| Mechanical and Housing | |
| Housing Material | Aluminum Alloy |
| Optical cover material | Polycarbonate |
| Housing Color | Black |
| Optical cover finish | Structured optic |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK03 [0.35 J reinforced] |
| Optical cover type | Lens |
| Net Weight (Piece) | 0.437 kg |
| Approval and Application | |
| CE mark | Yes |

GreenSpace Flex Luna

| | |
|---------------------------|---------------|
| Ambient temperature range | -20 to +45 °C |
|---------------------------|---------------|

Initial Performance (IEC Compliant)

| | |
|-------------------------|-------------|
| Luminous flux tolerance | -10% / +10% |
|-------------------------|-------------|

| | |
|-----------------------------|--------|
| Power consumption tolerance | +/-10% |
|-----------------------------|--------|

Product Data

| | |
|--------------------|---|
| Order product name | SM378B R P8 940 PSD-E MB D100 G-TT PRO |
|--------------------|---|

| | |
|-------------------|---|
| Full product name | SM378B R P8 940 PSD-E MB D100 G-TT PRO |
|-------------------|---|

| | |
|------------|--------------|
| Order code | 911401526646 |
|------------|--------------|

| | |
|---------------------|--------------|
| Material Nr. (12NC) | 911401526646 |
|---------------------|--------------|

| | |
|-------------------------------|---|
| Numerator - Quantity Per Pack | 1 |
|-------------------------------|---|

| | |
|---------------------------------|----|
| Numerator - Packs per outer box | 24 |
|---------------------------------|----|

Dimensional drawing

