PHILIPS

Lighting

GreenPerform Waterproof G3

WT198C HE LED27S/865 PSD L1200

GreenPerform Waterproof G3, 15.7 W, 2700 lm, 6500 K, DALI, 108° x 113°

GreenPerform Waterproof G3 is a superb choice for hard-working applications. Not only does it provide excellent optical performance, it also delivers substantial energy saving. And because it works seamlessly with IoT software like Interact, it also offers the option of customization, convenience, and data-driven insights.

Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP65 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance

Light Technical	
Luminous Flux	2,700 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	172 lm/W
Color rendering index (CRI)	80
Beam angle of light source	115 degree(s)
Light source color	White
Optic type	Very wide beam
Luminaire light beam spread	108° x 113°
Unified glare rating CEN	25

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Power Consumption	15.7 W
Power Factor (Fraction)	0.95
Number of products on MCB of 16 A type B	22
Protection class IEC	Safety class I

Controls and Dimming	
Dimmable	DALI

GreenPerform Waterproof G3

Control interface	DALI

Mechanical and Housing

Housing Material	Plastic
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Grey
Optical cover finish	Textured
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [6 J]
Optical cover type	Polycarbonate
Net Weight (Piece)	1.400 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-25 to +45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10%,+15%
Power consumption tolerance	+/-10%

Product Data

Order product name	WT198C HE LED27S/865 PSD L1200
Full product name	WT198C HE LED27S/865 PSD L1200
Full product code	692234199527999
Order code	911401528247
Material Nr. (12NC)	911401528247
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341995279
Numerator - Packs per outer box	9
EAN/UPC - Case	6942730830424

Dimensional drawing



Type	A	B	C	D	E min	E max	F	Nr. Of Clips
L600		665			308	512		6
L1200	76	1215	80	38	538	1062	85	10
L1500		1515			838	1362		12

© 2026 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.