# GreenSpace Flex Luna

## SM378B R P14 940 PSD-E MB D100 G-TT PRO

GreenSpace Flex Luna, 14.5 W, 1655 lm, 4000 K, DALI,
Structured optic, IP20 | Finger-protected

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

### Product data

| General Information | |
|---|---|
| **Light source engine type** | LED |
| **Value ladder** | Performance |

| Light Technical | |
|---|---|
| **Luminous Flux** | 1,655 lm |
| **Correlated Color Temperature (Nom)** | 4000 K |
| **Luminous Efficacy (rated) (Nom)** | 114 lm/W |
| **Color rendering index (CRI)** | 92 |
| **Light source color** | 940 neutral white |
| **Unified glare rating CEN** | 16 |

| Operating and Electrical | |
|---|---|
| **Input Voltage** | 220 to 240 V |
| **Line Frequency** | 50 or 60 Hz |
| **Power Consumption** | 14.5 W |
| **Power Factor (Fraction)** | 0.9 |
| **Number of products on MCB of 16 A type B** | 47 |

| | |
|---|---|
| **Protection class IEC** | Safety class II |

| Controls and Dimming | |
|---|---|
| **Dimmable** | DALI |
| **Control interface** | DALI |

| Mechanical and Housing | |
|---|---|
| **Housing Material** | Aluminum Alloy |
| **Optical cover material** | Polycarbonate |
| **Housing Color** | Black |
| **Optical cover finish** | Structured optic |
| **Ingress protection code** | IP20 [Finger-protected] |
| **Mech. impact protection code** | IK03 [0.35 J reinforced] |
| **Optical cover type** | Lens |
| **Net Weight (Piece)** | 0.476 kg |

| Approval and Application | |
|---|---|
| **CE mark** | Yes |

# GreenSpace Flex Luna

| | |
|---|---|
| **Ambient temperature range** | -20 to +45 °C |

| | |
|---|---|
| **Initial Performance (IEC Compliant)** | |
| **Luminous flux tolerance** | -10% / +10% |
| **Power consumption tolerance** | +/-10% |

| | |
|---|---|
| **Product Data** | |
| **Order product name** | SM378B R P14 940 PSD-E MB D100 G-TT PRO |

| | |
|---|---|
| **Full product name** | SM378B R P14 940 PSD-E MB D100 G-TT PRO |
| **Order code** | 911401528446 |
| **Material Nr. (12NC)** | 911401528446 |
| **Numerator - Quantity Per Pack** | 1 |
| **Numerator - Packs per outer box** | 18 |

## Dimensional drawing




© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.