



# GreenSpace Flex Luna

## SM378B R P15 PSD-TNW NB D100 G-TT PRO

GreenSpace Flex Luna, 15.5 W, 1320 lm, Tunable White, DALI, Structured optic, IP20 | Finger-protected

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

### Product data

General Information	
Light source engine type	LED
Value ladder	Performance

  

Light Technical	
Luminous Flux	1,320 lm
Correlated Color Temperature (Nom)	Tunable White
Luminous Efficacy (rated) (Nom)	85 lm/W
Color rendering index (CRI)	90
Light source color	Tunable white
Unified glare rating CEN	16

  

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	15.5 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	52

  

Protection class IEC	Safety class II
----------------------	-----------------

  

Controls and Dimming	
Dimmable	DALI
Control interface	DALI

  

Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Polycarbonate
Housing Color	Black
Optical cover finish	Structured optic
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.35 J reinforced]
Optical cover type	Lens
Net Weight (Piece)	0.500 kg

  

Approval and Application	
CE mark	No

## GreenSpace Flex Luna

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

### Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

Power consumption tolerance	+/-10%
-----------------------------	--------

### Product Data

Order product name	SM378B R P15 PSD-TNW NB D100 G-TT PRO
--------------------	--

Full product name	SM378B R P15 PSD-TNW NB D100 G-TT PRO
-------------------	--

Order code	911401530246
------------	--------------

Material Nr. (12NC)	911401530246
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	18
---------------------------------	----

## Dimensional drawing

