



GreenSpace Flex Luna

SM378B S P8 940 PSU-E MB D100 G-TT PRO

GreenSpace Flex Luna, 7.8 W, 990 lm, 4000 K, Structured optic, IP20 | Finger-protected

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance
Light Technical	
Luminous Flux	990 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	127 lm/W
Color rendering index (CRI)	92
Light source color	940 neutral white
Unified glare rating CEN	16
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	7.8 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	66

Protection class IEC	Safety class II
Controls and Dimming	
Dimmable	-
Control interface	-
Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Polycarbonate
Housing Color	Black
Optical cover finish	Structured optic
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.35 J reinforced]
Optical cover type	Lens
Net Weight (Piece)	0.558 kg
Approval and Application	
CE mark	Yes

GreenSpace Flex Luna

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data

Order product name	SM378B S P8 940 PSU-E MB D100 G-TT PRO
--------------------	---

Full product name	SM378B S P8 940 PSU-E MB D100 G-TT PRO
-------------------	---

Order code	911401531346
------------	--------------

Material Nr. (12NC)	911401531346
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	36
---------------------------------	----

Dimensional drawing

