



GreenPerform Panel RC099V G3

RC099X G3 LED40/840 L1W W60L60

GreenPerform Panel RC099V G3, 126 lm/W, 840 neutral white, DALI

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600,300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance
Light Technical	
Luminous Flux	4,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	126 lm/W
Color rendering index (CRI)	80
Light source color	840 neutral white
Unified glare rating CEN	22
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	31.5 W

Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	17
Protection class IEC	Safety class II
Controls and Dimming	
Dimmable	DALI
Control interface	DALI
Mechanical and Housing	
Housing Material	Metal
Optical cover material	Polystyrene
Housing Color	White RAL 9003
Optical cover finish	Smoke
Overall length	595 mm
Overall width	595 mm
Overall height	35 mm

GreenPerform Panel RC099V G3

Overall diameter	595 mm
Dimensions (Height x Width x Depth)	35 x 595 x 595 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	PS
Net Weight (Piece)	1.800 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-20 °C to 45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	RC099X G3 LED40/840 L1W W60L60
Full product name	RC099X G3 LED40/840 L1W W60L60
Full product code	692382862736299
Order code	62736299
Material Nr. (12NC)	911401533543
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828627362
Numerator - Packs per outer box	4
EAN/UPC - Case	6923828627362

Dimensional drawing

