



GreenSpace Flex Luna

SM378B S P20 930 PSU-E MB D100 G-TT PRO

GreenSpace Flex Luna, 20 W, 2150 lm, 3000 K, Structured optic, IP20 | Finger-protected

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

Product data

General Information		Protection class IEC	
Light source engine type	LED	Protection class IEC	Safety class II
Value ladder	Performance	Controls and Dimming	
Light Technical		Dimmable	-
Luminous Flux	2,150 lm	Control interface	-
Correlated Color Temperature (Nom)	3000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	108 lm/W	Housing Material	Aluminum Alloy
Color rendering index (CRI)	92	Optical cover material	Polycarbonate
Light source color	930 warm white	Housing Color	Black
Unified glare rating CEN	16	Optical cover finish	Structured optic
Operating and Electrical		Ingress protection code	IP20 [Finger-protected]
Input Voltage	220 to 240 V	Mech. impact protection code	IK03 [0.35 J reinforced]
Line Frequency	50 or 60 Hz	Optical cover type	Lens
Power Consumption	20 W	Net Weight (Piece)	0.587 kg
Power Factor (Fraction)	0.9	Approval and Application	
Number of products on MCB of 16 A type B	83	CE mark	Yes

GreenSpace Flex Luna

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data

Order product name	SM378B S P20 930 PSU-E MB D100 G-TT PRO
--------------------	--

Full product name	SM378B S P20 930 PSU-E MB D100 G-TT PRO
-------------------	--

Order code	911401533946
------------	--------------

Material Nr. (12NC)	911401533946
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	36
---------------------------------	----

Dimensional drawing

