PHILIPS

Lighting

SlimBalance G3

SP570P LED50/840 L150W6 SD PSU

SlimBalance G3, Mounting bracket, 132 lm/W, 840 neutral white

SlimBalance G3 SP570P is a flexible linear office offer which fits a variety of spaces like office, education. It offers flexible width of 35/60/90/120mm and length of 600/1200/1500mm to fit multiple applications. Geometric shapes help further create differentiated space. By means of its special designed structure, it offers quick and easy installation and maintenance. UGR19 is available for certain types through customized solution to provide a better visual comfort office environment.

Product data

General Information	
Number of gear units	1 unit
Gear	-
Driver included	Yes
Light source engine type	LED
Service tag	Yes
Value ladder	Performance
Warranty period	3 years

Light Technical	
Luminous Flux	5,344 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	132 lm/W
Color rendering index (CRI)	80
Number of light sources	2
Beam angle of light source	120 degree(s)
Light source color	840 neutral white
Optic type	Beam angle 100°
Luminaire light beam spread	100°
Unified glare rating CEN	27
Effective projected area	0.075 m²

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	18 A
Inrush time	0.238 ms
Power Consumption	40.5 W
Power Factor (Fraction)	0.9
Connection	Flying leads/wires
Cable	Cable 0.3 m without plug
Number of products on MCB of 16 A type B	24
Suitable for random switching	No
Protection class IEC	Safety class I

Controls and Dimming	
Dimmable	No
Control interface	-

SlimBalance G3

Maximum dim level	Not applicable

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	White
Mounting device	Mounting bracket
Optical cover finish	Opal
Overall length	150.5 mm
Overall width	6.34 mm
Overall height	7.86 mm
Dimensions (Height x Width x Depth)	8 x 6 x 151 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Optical cover type	Opal
Net Weight (Piece)	2.490 kg

Approval and Application

Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
EU RoHS compliant	No
Performance ambient temperature Tq	25 °C
Ambient temperature range	-20 °C to 40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Initial chromaticity	SDCM<=4
Power consumption tolerance	+/-10%

Product Data

Order product name	SP570P LED50/840 L150W6 SD PSU
Full product name	SP570P LED50/840 L150W6 SD PSU
Full product code	692234199412899
Order code	911401534842
Material Nr. (12NC)	911401534842
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341994128
Numerator - Packs per outer box	2
EAN/UPC - Case	6922341994128

Dimensional drawing



SP570 W6L150 SD shop drawing

© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.