



Greenspace Flex

RS378B P11 940 PSD-E MB M55

Greenspace Flex, 11 W, 940 neutral white, DALI, IP20 | Finger-protected

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

Product data

| General Information | |
|--------------------------|-------------|
| Light source engine type | LED |
| Value ladder | Performance |

| Light Technical | |
|------------------------------------|-------------------|
| Luminous Flux | 1,012 lm |
| Correlated Color Temperature (Nom) | 4000 K |
| Luminous Efficacy (rated) (Nom) | 92 lm/W |
| Color rendering index (CRI) | >90 |
| Light source color | 940 neutral white |

| Operating and Electrical | |
|--|-----------------|
| Input Voltage | 220-240 V |
| Line Frequency | 50 or 60 Hz |
| Power Consumption | 11 W |
| Power Factor (Fraction) | 0.83 |
| Number of products on MCB of 16 A type B | - |
| Protection class IEC | Safety class II |

| Controls and Dimming | |
|----------------------|------|
| Dimmable | DALI |
| Control interface | DALI |

| Mechanical and Housing | |
|------------------------------|----------------------------|
| Housing Material | Aluminum Alloy |
| Optical cover material | Polymethyl methacrylate |
| Housing Color | Grey |
| Optical cover finish | Opal |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK04 [0.5 J standard plus] |
| Optical cover type | PMMA |
| Net Weight (Piece) | 0.250 kg |

| Approval and Application | |
|---------------------------|---------------|
| CE mark | Yes |
| Ambient temperature range | -20 to +45 °C |

| Initial Performance (IEC Compliant) | |
|-------------------------------------|-------------|
| Luminous flux tolerance | -10% / +10% |

Greenspace Flex

| | |
|-----------------------------|--------|
| Power consumption tolerance | +/-10% |
|-----------------------------|--------|

Product Data

| | |
|--------------------|-----------------------------|
| Order product name | RS378B P11 940 PSD-E MB M55 |
| Full product name | RS378B P11 940 PSD-E MB M55 |
| Full product code | 911401536571 |

| | |
|------------|--------------|
| Order code | 911401536571 |
|------------|--------------|

| | |
|---------------------|--------------|
| Material Nr. (12NC) | 911401536571 |
|---------------------|--------------|

| | |
|-------------------------------|---|
| Numerator - Quantity Per Pack | 1 |
|-------------------------------|---|

| | |
|---------------------------------|----|
| Numerator - Packs per outer box | 36 |
|---------------------------------|----|

Dimensional drawing

