



GreenUp hospitality spot

RS318B P5 927 PSU-E WB S

GreenUp hospitality spot, 5 W, 927 warm white, IP20 | Finger-protected

GreenUp hospitality spot is a small cut out spot but with comprehensive offers. It offers flexible wattages for different indoor applications, such as retail and hospitality. This family delivers high CRI90 and 3 different beam angles to perfectly fit the light requirement of indoor retail and hospitality applications.

Product data

| General Information | | Number of products on MCB of 16 A type B | |
|------------------------------------|----------------|--|-------------------------|
| Light source engine type | LED | | - |
| Value ladder | Value | Protection class IEC | Safety class II |
| Light Technical | | Controls and Dimming | |
| Luminous Flux | 80 lm | Dimmable | No |
| Correlated Color Temperature (Nom) | 2700 K | Control interface | - |
| Luminous Efficacy (rated) (Nom) | 96 lm/W | Mechanical and Housing | |
| Color rendering index (CRI) | >90 | Housing Material | Aluminum die-cast |
| Light source color | 927 warm white | Optical cover material | Polymethyl methacrylate |
| Operating and Electrical | | Housing Color | Aluminum and gray |
| Input Voltage | 220 to 240 V | Optical cover finish | Clear |
| Line Frequency | 0/50/60 Hz | Overall length | 93 mm |
| Inrush current | 0.025 A | Overall width | 85 mm |
| Power Consumption | 5 W | Overall height | 93 mm |
| Power Factor (Fraction) | 0.9 | Overall diameter | 85 mm |
| | | Dimensions (Height x Width x Depth) | 93 x 85 x 93 mm |

GreenUp hospitality spot

| | |
|------------------------------|--------------------------|
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK03 [0.35 J reinforced] |
| Optical cover type | - |
| Net Weight (Piece) | 0.015 kg |

Approval and Application

| | |
|---------------------------|---------------|
| Flammability mark | - |
| CE mark | No |
| Ambient temperature range | +20 to +40 °C |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|--------|
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | - |
| Power consumption tolerance | +/-10% |

Product Data

| | |
|---------------------------------|--------------------------|
| Order product name | RS318B P5 927 PSU-E WB S |
| Full product name | RS318B P5 927 PSU-E WB S |
| Full product code | 872016953361599 |
| Order code | 911401537102 |
| Material Nr. (12NC) | 911401537102 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8720169533615 |
| Numerator - Packs per outer box | 16 |
| EAN/UPC - Case | 8720169545106 |

Dimensional drawing

