



# Greenspace Flex

## RS378B P15 930 PSD-E MB M55

Greenspace Flex, 15 W, 930 warm white, DALI, IP20 | Finger-protected

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

### Product data

| General Information                      |                 |
|--|-----------------|
| Light source engine type                 | LED             |
| Value ladder                             | Performance     |
| Light Technical                          |                 |
| Luminous Flux                            | 1,350 lm        |
| Correlated Color Temperature (Nom)       | 3000 K          |
| Luminous Efficacy (rated) (Nom)          | 90 lm/W         |
| Color rendering index (CRI)              | >90             |
| Light source color                       | 930 warm white  |
| Operating and Electrical                 |                 |
| Input Voltage                            | 220-240 V       |
| Line Frequency                           | 50 or 60 Hz     |
| Power Consumption                        | 15 W            |
| Power Factor (Fraction)                  | 0.9             |
| Number of products on MCB of 16 A type B | -               |
| Protection class IEC                     | Safety class II |

| Controls and Dimming         |                            |
|------------------------------|----------------------------|
| Dimmable                     | DALI                       |
| Control interface            | DALI                       |
| Mechanical and Housing       |                            |
| Housing Material             | Aluminum Alloy             |
| Optical cover material       | Polymethyl methacrylate    |
| Housing Color                | Grey                       |
| Optical cover finish         | Opal                       |
| Ingress protection code      | IP20 [Finger-protected]    |
| Mech. impact protection code | IK04 [0.5 J standard plus] |
| Optical cover type           | PMMA                       |
| Net Weight (Piece)           | 0.310 kg                   |

| Approval and Application  |               |
|---------------------------|---------------|
| CE mark                   | Yes           |
| Ambient temperature range | -20 to +45 °C |

| Initial Performance (IEC Compliant) |             |
|-------------------------------------|-------------|
| Luminous flux tolerance             | -10% / +10% |

## Greenspace Flex

|                             |        |
|-----------------------------|--------|
| Power consumption tolerance | +/-10% |
|-----------------------------|--------|

### Product Data

|                    |                             |
|--------------------|-----------------------------|
| Order product name | RS378B P15 930 PSD-E MB M55 |
| Full product name  | RS378B P15 930 PSD-E MB M55 |
| Full product code  | 911401537171                |

|            |              |
|------------|--------------|
| Order code | 911401537171 |
|------------|--------------|

|                     |              |
|---------------------|--------------|
| Material Nr. (12NC) | 911401537171 |
|---------------------|--------------|

|                               |   |
|-------------------------------|---|
| Numerator - Quantity Per Pack | 1 |
|-------------------------------|---|

|                                 |    |
|---------------------------------|----|
| Numerator - Packs per outer box | 36 |
|---------------------------------|----|

## Dimensional drawing

