



# GreenUp hospitality spot

## RS318B P5 930 PSU-E WB S

GreenUp hospitality spot, 5 W, 930 warm white, IP20 | Finger-protected

GreenUp hospitality spot is a small cut out spot but with comprehensive offers. It offers flexible wattages for different indoor applications, such as retail and hospitality. This family delivers high CRI90 and 3 different beam angles to perfectly fit the light requirement of indoor retail and hospitality applications.

### Product data

General Information		Number of products on MCB of 16 A type B	
Light source engine type	LED		-
Value ladder	Value	Protection class IEC	Safety class II
Light Technical		Controls and Dimming	
Luminous Flux	80 lm	Dimmable	No
Correlated Color Temperature (Nom)	3000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	101 lm/W	Mechanical and Housing	
Color rendering index (CRI)	>90	Housing Material	Aluminum die-cast
Light source color	930 warm white	Optical cover material	Polymethyl methacrylate
Operating and Electrical		Housing Color	Aluminum and gray
Input Voltage	220 to 240 V	Optical cover finish	Clear
Line Frequency	0/50/60 Hz	Overall length	93 mm
Inrush current	0.025 A	Overall width	85 mm
Power Consumption	5 W	Overall height	93 mm
Power Factor (Fraction)	0.9	Overall diameter	85 mm
		Dimensions (Height x Width x Depth)	93 x 85 x 93 mm

## GreenUp hospitality spot

Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.35 J reinforced]
Optical cover type	-
Net Weight (Piece)	0.015 kg

### Approval and Application

Flammability mark	-
CE mark	No
Ambient temperature range	+20 to +40 °C

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	-
Power consumption tolerance	+/-10%

### Product Data

Order product name	RS318B P5 930 PSU-E WB S
Full product name	RS318B P5 930 PSU-E WB S
Full product code	872016953315899
Order code	911401537402
Material Nr. (12NC)	911401537402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169533158
Numerator - Packs per outer box	16
EAN/UPC - Case	8720169544642

## Dimensional drawing

