



# Greenspace Flex

## RS378B P24 930 PSD-E WB M70

Greenspace Flex, 24 W, 930 warm white, DALI, IP20 | Finger-protected

GreenSpace Flex is performance portfolio dedicated to Hospitality segment for GC/GM countries. With modular design concept, the light engines and different trims could have multiply of combination to satisfy diversified customer's requirement.

### Product data

General Information	
Light source engine type	LED
Value ladder	Performance

  

Light Technical	
Luminous Flux	2,350 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	98 lm/W
Color rendering index (CRI)	>90
Light source color	930 warm white

  

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Power Consumption	24 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	DALI
Control interface	DALI

  

Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Polymethyl methacrylate
Housing Color	Grey
Optical cover finish	Opal
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK04 [0.5 J standard plus]
Optical cover type	PMMA
Net Weight (Piece)	0.600 kg

  

Approval and Application	
CE mark	Yes
Ambient temperature range	-20 to +45 °C

  

Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%

## Greenspace Flex

Power consumption tolerance	+/-10%
<b>Product Data</b>	
Order product name	RS378B P24 930 PSD-E WB M70
Full product name	RS378B P24 930 PSD-E WB M70
Full product code	692382865359099
Order code	911401538171

Material Nr. (12NC)	911401538171
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828653590
Numerator - Packs per outer box	24
EAN/UPC - Case	6923828653590

## Dimensional drawing

