



GreenSpace Flex Luna

SM378B S P12 PSD-TNW MB D100 G-TT PRO

GreenSpace Flex Luna, 13 W, 1090 lm, Tunable White, DALI, Structured optic, IP20 | Finger-protected

Ever-changing yet dependable, the moon reflects the very essence of hospitality lighting, which is adaptable, elegant, and always in tune with its surroundings. GreenSpace Flex Luna is designed to evoke a unique sensation. Like the moon, Luna does not overpower but enhances its surroundings, casting a glow that feels both intimate and grand. It is not just a light. It is an intimate experience.

Product data

General Information		Protection class IEC	
Light source engine type	LED		Safety class II
Value ladder	Performance		
Light Technical		Controls and Dimming	
Luminous Flux	1,090 lm	Dimmable	DALI
Correlated Color Temperature (Nom)	Tunable White	Control interface	DALI
Luminous Efficacy (rated) (Nom)	84 lm/W	Mechanical and Housing	
Color rendering index (CRI)	90	Housing Material	Aluminum Alloy
Light source color	Tunable white	Optical cover material	Polycarbonate
Unified glare rating CEN	16	Housing Color	Black
Operating and Electrical		Optical cover finish	Structured optic
Input Voltage	220 to 240 V	Ingress protection code	IP20 [Finger-protected]
Line Frequency	50 or 60 Hz	Mech. impact protection code	IK03 [0.35 J reinforced]
Power Consumption	13 W	Optical cover type	Lens
Power Factor (Fraction)	0.9	Net Weight (Piece)	0.615 kg
Number of products on MCB of 16 A type B	70	Approval and Application	
		CE mark	No

GreenSpace Flex Luna

Ambient temperature range	-20 to +45 °C
---------------------------	---------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data

Order product name	SM378B S P12 PSD-TNW MB D100 G-TT PRO
--------------------	--

Full product name	SM378B S P12 PSD-TNW MB D100 G-TT PRO
-------------------	--

Order code	911401539346
------------	--------------

Material Nr. (12NC)	911401539346
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---

Numerator - Packs per outer box	24
---------------------------------	----

Dimensional drawing

