



# FastSet

## SM150C LED15S/840 PSU L602

FastSet, 14 W, 1600 lm, 4000 K, Frosted, IP40 | Wire-protected

Philips FastSet SM150C is a batten family mainly for school lighting application where surface mounted or suspended applications are required. It provides 600mm/1200mm/1500mm length options with IP40 protection (front side). It offers max 130lm/w system efficacy which helps better energy saving for schools as well.

### Product data

General Information	
Light source engine type	LED
Light Technical	
Luminous Flux	1,600 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	114 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Effective projected area	0.084 m²
Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	9.08 A
Power Consumption	14 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B 72	
Protection class IEC	Safety class I

Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Metal-Plastic
Optical cover material	Polycarbonate
Housing Color	White RAL 9003
Optical cover finish	Frosted
Overall length	602 mm
Overall width	160 mm
Overall height	64 mm
Dimensions (Height x Width x Depth)	64 x 160 x 602 mm
Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK03 [0.35 J reinforced]
Optical cover type	Polycarbonate bowl/cover foggy
Net Weight (Piece)	0.990 kg
Approval and Application	
Flammability mark	For mounting on normally flammable surfaces

CE mark	Yes
Ambient temperature range	0 to +35 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	SDCM<=3
Power consumption tolerance	+/-10%
Product Data	
Order product name	SM150C LED15S/840 PSU L602

Full product name	SM150C LED15S/840 PSU L602
Full product code	871951492967899
Order code	911401543091
Material Nr. (12NC)	911401543091
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514929678
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514929760

Dimensional drawing

