



FastSet

SM150C LED80S/840 PSU L1440

FastSet, 63 W, 8000 lm, 4000 K, Frosted, IP40 | Wire-protected

Philips FastSet SM150C is a batten family mainly for school lighting application where surface mounted or suspended applications are required. It provides 600mm/1200mm/1500mm length options with IP40 protection (front side). It offers max 130lm/w system efficacy which helps better energy saving for schools as well.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance

Light Technical	
Luminous Flux	8,000 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	126 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Effective projected area	0.21 m ²

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	15 A
Power Consumption	63 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	31

Protection class IEC	Safety class I
----------------------	----------------

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Metal-Plastic
Optical cover material	Polycarbonate
Housing Color	White RAL 9003
Optical cover finish	Frosted
Overall length	1,440 mm
Overall width	160 mm
Overall height	64 mm
Dimensions (Height x Width x Depth)	64 x 160 x 1440 mm
Ingress protection code	IP40 [Wire-protected]
Mech. impact protection code	IK03 [0.35 J reinforced]
Optical cover type	Polycarbonate bowl/cover foggy
Net Weight (Piece)	2.340 kg

Approval and Application

Flammability mark For mounting on normally flammable surfaces

CE mark Yes

Ambient temperature range 0 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance +/-10%

Initial chromaticity SDCM<=3

Power consumption tolerance +/-10%

Product Data

Order product name SM150C LED80S/840 PSU L1440

Full product name SM150C LED80S/840 PSU L1440

Full product code 871951492972299

Order code 911401543591

Material Nr. (12NC) 911401543591

Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8719514929722

Numerator - Packs per outer box 4

EAN/UPC - Case 8719514929814

Dimensional drawing

