



GreenUp Track

ST306T P20 930 PSD WB WH SR

GreenUp Track, 20 W, 1700 lm, 3000 K, depends on driver (1-10V, DALI...)

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Track product family offers a complete track light solutions with aesthetic and compact product design, comprehensive control availability and specification options. It offers an outstanding color rendering performance and glare control effect, tailored for retail and hospitality applications.

Product data

General Information		Protection class IEC	
Light source engine type	LED	Safety class I	
Value ladder	Value	Controls and Dimming	
Light Technical		Dimmable	Yes
Luminous Flux	1,700 lm	Control interface	depends on driver (1-10V, DALI...)
Correlated Color Temperature (Nom)	3000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	85 lm/W	Housing Material	Aluminum die cast
Color rendering index (CRI)	>90	Optical cover material	Polycarbonate
Light source color	930 warm white	Housing Color	White
Operating and Electrical		Optical cover finish	Smoke
Input Voltage	220-240 V	Overall length	150 mm
Line Frequency	50 or 60 Hz	Overall width	95 mm
Power Consumption	20 W	Overall height	200 mm
Power Factor (Fraction)	0.9	Dimensions (Height x Width x Depth)	200 x 95 x 150 mm
Number of products on MCB of 16 A type B	104	Ingress protection code	IP20 [Finger-protected]
		Mech. impact protection code	IK03 [0.3 J]

GreenUp Track

Optical cover type	Lens
Net Weight (Piece)	1.042 kg

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	ST306T P20 930 PSD WB WH SR
--------------------	-----------------------------

Full product name	ST306T P20 930 PSD WB WH SR
Full product code	872016952368599
Order code	911401545522
Material Nr. (12NC)	911401545522
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169523685
Numerator - Packs per outer box	12
EAN/UPC - Case	8720169535176

Dimensional drawing

