



TrueFashion EM

RS700B P40 LED47 940PW PSU MB WH

TrueFashion EM, 40.3 W, PremiumWhite with CRI ≥90 and color temperature 4000K, IP20 | Finger-protected

TrueFashion is the LED projector family answering miniaturization and presentation needs of specialized retailers. Firstly, these miniaturized spots with clean and fine detailing offer contemporary design and blend seamlessly into your store interior for a tailor-made look. Secondly, it provides high quality accentuation effect thanks to its innovative OptiAccent lens technology (FPO), which provides higher central intensity beam without spill light to maximize the contrast ratio hence optimize the accent effect. Especially in challenging narrow spot (12D) and spot (18D) applications, the difference of OptiAccent to Chip on Board and reflector optics is like day and night. OptiAccent also reduces direct glare by a factor of 5 to enable superior visual comfort. Lastly, TrueFashion also has the light spectra taken care of: the specially designed Philips LED flavors enhance colors (saturation) and whites, while offering high degree of fidelity (exceeds CRI90). This is how TrueFashion ensures a superior light experience in your retail applications.

Warnings and Safety

- The luminaire should be mounted outside of arm's reach
- The luminaire should be installed and disassembled by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements

Product data

General Information		Correlated Color Temperature (Nom)	
Driver included	Yes	4000 K	
Light source engine type	LED	Luminous Efficacy (rated) (Nom)	
		118 lm/W	
		Color rendering index (CRI)	
		90	
		Light source color	
		PremiumWhite with CRI ≥90 and color temperature 4000K	
Light Technical			
Luminous Flux	4,736 lm		

Unified glare rating CEN	Not applicable
--------------------------	----------------

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	40.3 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	40
Protection class IEC	Safety class II

Controls and Dimming

Dimmable	-
Control interface	-

Mechanical and Housing

Housing Material	Aluminum Alloy
Optical cover material	Polymethyl methacrylate
Housing Color	White
Optical cover finish	Structured optic
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.35 J reinforced]

Optical cover type	Lens
Net Weight (Piece)	0.620 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-15 to +35 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Product Data

Order product name	RS700B P40 LED47 940PW PSU MB WH
Full product name	RS700B P40 LED47 940PW PSU MB WH
Order code	911401547346
Material Nr. (12NC)	911401547346
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1

Dimensional drawing

