PHILIPS

Lighting

GreenSpace Surface Mount

SM303C P24 940 PSU VWB

GreenSpace Surface Mount, 24 W, 2280 lm, 4000 K, Frosted, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Surface Mount is the entry level downlight family dedicated with suspension and surface mount versions, which offers a complete range of options for optical solutions, lumen outputs and color temperatures with multiple form factors available.

Product data

General Information	
Light source engine type	-
Value ladder	Performance

Light Technical	
Luminous Flux	2,280 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	95 lm/W
Color rendering index (CRI)	>90
Light source color	940 neutral white

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Power Consumption	24 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	-
Protection class IEC	Safety class II

Controls and Dimming	
Dimmable	No
Control interface	-

Mechanical and Housing	
Housing Material	Aluminum Alloy
Optical cover material	Acrylate
Housing Color	White
Optical cover finish	Frosted
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]

GreenSpace Surface Mount

Optical cover type	Acrylate
Net Weight (Piece)	2.050 kg

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	SM303C P24 940 PSU VWB

Full product name	SM303C P24 940 PSU VWB
Full product code	872016953052299
Order code	911401547932
Material Nr. (12NC)	911401547932
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169530522
Numerator - Packs per outer box	4
EAN/UPC - Case	8720169542013

Dimensional drawing



© 2026 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.