PHILIPS

Lighting

GreenPerform Highbay G5

BY698X G5 LED250/CW L1W MW WB GM L3m

GreenPerform Highbay G5, 144 W, 25000 lm, 6500 K, Internal (no external connection), 85°

The GreenPerform Highbay G5 continues the GreenPerform family's enviable reputation for reliable performance. Not only does it deliver leading system efficacy and extended long-term quality, it also promises Unified Glare Rating (UGR) control with compact dimensions. GreenPerform Highbay G5 is also fully compatible with IoT software such as Interact, which is a scalable, future-proof control system. The family also has a series that supports cold room applications with 100% humidity and no condensation. All benefits than make this robust, optimized, and versatile family suitable for almost all industrial applications.

Product data

General Information	
Number of gear units	1 unit
Gear	-
Driver included	Yes
Light source engine type	LED
Value ladder	Performance
Warranty period	5 years

Number of light sources	1
Beam angle of light source	115 degree(s)
Light source color	865 cool daylight
Optic type	Wide beam
Luminaire light beam spread	85°
Unified glare rating CEN	25
Effective projected area	0 m²

Light Technical	
Luminous Flux	25,000 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	173 lm/W
Color rendering index (CRI)	80

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	54 A
Inrush time	0.75 ms

GreenPerform Highbay G5

Power Consumption	144 W
Power Factor (Fraction)	0.95
Connection	Flying leads/wires
Cable	Cable 3.0 m without plug
Number of products on MCB of 16 A type B	6
Suitable for random switching	Yes
Protection class IEC	Safety class I

Controls and Dimming

Dimmable	Wireless Dim - Do not use with dimmer
Control interface	Internal (no external connection)
Maximum dim level	0% (digital)

Mechanical and Housing

Housing Material	Aluminum die-cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Housing Color	Grey
Mounting device	Suspension set simple, standard
Optical cover finish	Clear
Overall length	530 mm
Overall width	393 mm
Overall height	110 mm
Dimensions (Height x Width x Depth)	110 x 393 x 530 mm
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK06 [1 J]
Optical cover type	Clear dome
Net Weight (Piece)	4.690 kg

Approval and Application

Glow-wire test	Temperature 750 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
CE mark	Yes
ENEC mark	-
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	0.2 m
EU RoHS compliant	Yes
Performance ambient temperature Tq	35 °C
Ambient temperature range	-30 to +50 °C

UV

UV-C radiation	0 W
UV-C irradiance defined at 0.2m	0 mW/m²

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.317, 0.338) SDCM<5
Power consumption tolerance	+/-10%

Product Data

Order product name	BY698X G5 LED250/CW L1W MW WB GM L3m
Full product name	BY698X G5 LED250/CW L1W MW WB GM L3m
Full product code	872110330845000
Order code	911401549245
Material Nr. (12NC)	911401549245
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103308450
Numerator - Packs per outer box	1
EAN/UPC - Case	8721103308450

Dimensional drawing



GreenPerform Highbay G5

© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com
2025, May 21 - data subject to change