



GreenPerform Panel RC099V G3

RC099X G3 LED37/940 L1W W30L120 OC

GreenPerform Panel RC099V G3, 115 lm/W, 940 neutral white, DALI

GreenPerform panel RC099V G3 is an affordable LED panel delivering comfortable light with excellent uniformity. It offers 3 types, 600x600, 300x1200, and 600x1200mm with max: 140lm/w. Its UGR19 brings more visual comfort in the office. Equipped with Dali, Interact and EcoSet, RC099V G2 offers easy connection to control system to bring better energy saving.

Product data

General Information		Power Factor (Fraction)		0.9
Light source engine type	LED	Number of products on MCB of 16 A type B		17
Value ladder	Performance	Protection class IEC		Safety class II
Light Technical		Controls and Dimming		
Luminous Flux	3,700 lm	Dimmable	DALI	
Correlated Color Temperature (Nom)	4000 K	Control interface		DALI
Luminous Efficacy (rated) (Nom)	115 lm/W	Mechanical and Housing		
Color rendering index (CRI)	90	Housing Material	Metal	
Light source color	940 neutral white	Optical cover material	Polystyrene	
Unified glare rating CEN	19	Housing Color	White RAL 9003	
Operating and Electrical		Optical cover finish	Smoke	
Input Voltage	220-240 V	Overall length	1,195 mm	
Line Frequency	50 or 60 Hz	Overall width	295 mm	
Power Consumption	31.5 W	Overall height	35 mm	

GreenPerform Panel RC099V G3

Overall diameter	1,195 mm
Dimensions (Height x Width x Depth)	35 x 295 x 1195 mm
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK02 [0.2 J standard]
Optical cover type	PS
Net Weight (Piece)	2.200 kg

Approval and Application

CE mark	Yes
Ambient temperature range	-20 °C to 45 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	-10% / +10%
-------------------------	-------------

Power consumption tolerance	+/-10%
-----------------------------	--------

Product Data

Order product name	RC099X G3 LED37/940 L1W W30L120 OC
Full product name	RC099X G3 LED37/940 L1W W30L120 OC
Order code	911401551443
Material Nr. (12NC)	911401551443
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4

Dimensional drawing

