



GreenPerform Waterproof +5

WT178C LED22S/865 PSU L600

GreenPerform Waterproof +5, 15 W, 2250 lm, 6500 K, Fixed Output

Like all the luminaires in the GreenPerform series, GreenPerform Waterproof +5 offers excellent energy savings, a long lifetime, good optical performance, and robust design. GreenPerform Waterproof +5 features superior floor illumination, high efficacy of 150–154 lm/W, an IP66 rating, quick on-site assembly, and user-friendly maintenance. Choose GreenPerform Waterproof +5 battens for a wide range of industrial and office applications.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance
Light Technical	
Luminous Flux	2,250 lm
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	150 lm/W
Color rendering index (CRI)	80
Light source color	White
Unified glare rating CEN	Not applicable
Operating and Electrical	
Input Voltage	100 to 277 V
Line Frequency	50 to 60 Hz
Mechanical and Housing	
Housing Material	Plastic
Optical cover material	Polycarbonate
Housing Color	Gray and White
Optical cover finish	Frosted
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Controls and Dimming	
Dimmable	Fixed
Control interface	Fixed Output
Power Consumption	
Power Consumption	15 W
Power Factor (Fraction)	
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	
Number of products on MCB of 16 A type B	51
Protection class IEC	
Protection class IEC	Safety class I

GreenPerform Waterproof +5

Mech. impact protection code	IK08 [6 J]
Optical cover type	Polycarbonate bowl/cover
Net Weight (Piece)	0.660 kg
Approval and Application	
CE mark	No
Ambient temperature range	-30 to +50 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	WT178C LED22S/865 PSU L600
Full product name	WT178C LED22S/865 PSU L600
Full product code	872110332237199
Order code	911401553646
Material Nr. (12NC)	911401553646
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103322371
Numerator - Packs per outer box	9
EAN/UPC - Case	8721103322586

Dimensional drawing

