



GreenPerform Waterproof +5

WT178C LED43S/830 PSU L1200

GreenPerform Waterproof +5, 28.5 W, 4075 lm, 3000 K, Fixed Output

Like all the luminaires in the GreenPerform series, GreenPerform Waterproof +5 offers excellent energy savings, a long lifetime, good optical performance, and robust design. GreenPerform Waterproof +5 features superior floor illumination, high efficacy of 150-154 lm/W, an IP66 rating, quick on-site assembly, and user-friendly maintenance. Choose GreenPerform Waterproof +5 battens for a wide range of industrial and office applications.

Product data

General Information	
Light source engine type	LED
Value ladder	Performance
Light Technical	
Luminous Flux	4,075 lm
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	143 lm/W
Color rendering index (CRI)	80
Light source color	White
Unified glare rating CEN	Not applicable
Operating and Electrical	
Input Voltage	100 to 277 V
Line Frequency	50 to 60 Hz
Power Consumption	
Power Consumption	28.5 W
Power Factor (Fraction)	
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	
Number of products on MCB of 16 A type B	26
Protection class IEC	
Protection class IEC	Safety class I
Controls and Dimming	
Dimmable	Fixed
Control interface	Fixed Output
Mechanical and Housing	
Housing Material	Plastic
Optical cover material	Polycarbonate
Housing Color	Gray and White
Optical cover finish	Frosted
Ingress protection code	IP66 [Dust penetration-protected, jet-proof]

GreenPerform Waterproof +5

Mech. impact protection code	IK08 [6 J]
Optical cover type	Polycarbonate bowl/cover
Net Weight (Piece)	1.100 kg
Approval and Application	
CE mark	No
Ambient temperature range	-30 to +50 °C
Initial Performance (IEC Compliant)	
Luminous flux tolerance	-10% / +10%
Power consumption tolerance	+/-10%

Product Data	
Order product name	WT178C LED43S/830 PSU L1200
Full product name	WT178C LED43S/830 PSU L1200
Full product code	872110332241899
Order code	911401554046
Material Nr. (12NC)	911401554046
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103322418
Numerator - Packs per outer box	9
EAN/UPC - Case	8721103322623

Dimensional drawing

