



GreenUp Track

ST306T P10 940 PSD NB BK BR

GreenUp Track, 10 W, 900 lm, 4000 K, depends on driver (1-10V, DALI...)

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenUp Track product family offers a complete track light solutions with aesthetic and compact product design, comprehensive control availability and specification options. It offers an outstanding color rendering performance and glare control effect, tailored for retail and hospitality applications.

Product data

General Information		Protection class IEC	
Light source engine type	LED	Safety class I	
Value ladder	Value	Controls and Dimming	
Light Technical		Dimmable	Yes
Luminous Flux	900 lm	Control interface	depends on driver (1-10V, DALI...)
Correlated Color Temperature (Nom)	4000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	90 lm/W	Housing Material	Aluminum die cast
Color rendering index (CRI)	>90	Optical cover material	Polycarbonate
Light source color	940 neutral white	Housing Color	Black
Operating and Electrical		Optical cover finish	Smoke
Input Voltage	220-240 V	Overall length	150 mm
Line Frequency	50 or 60 Hz	Overall width	95 mm
Power Consumption	10 W	Overall height	200 mm
Power Factor (Fraction)	0.9	Dimensions (Height x Width x Depth)	200 x 95 x 150 mm
Number of products on MCB of 16 A type B	210	Ingress protection code	IP20 [Finger-protected]
		Mech. impact protection code	IK03 [0.3 J]

GreenUp Track

Optical cover type	Lens
Net Weight (Piece)	1.042 kg

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	ST306T P10 940 PSD NB BK BR
--------------------	-----------------------------

Full product name	ST306T P10 940 PSD NB BK BR
Full product code	872016951790599
Order code	911401556422
Material Nr. (12NC)	911401556422
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169517905
Numerator - Packs per outer box	12
EAN/UPC - Case	8720169518513

Dimensional drawing

