



GreenSpace Accent Elbow GCGM

RS305B P6 930 PSU-E VWB

GreenSpace Accent Elbow GCGM, 5.4 W, 6.6 W, 930 warm white, IP20 | Finger-protected

Retail & Hospitality has a clear trend that clusters of choices is one of the most important DNAs that being strongly expected in this specific applications. GreenSpace Accent Elbow is a product family with full choices in terms of optic choices, lumen diversities, control availability and wide range of tiltable angles, tailored for retail and hospitality applications.

Product data

General Information		Number of products on MCB of 16 A type B	
Light source engine type	LED		-
Value ladder	Performance	Protection class IEC	Safety class II
Light Technical		Controls and Dimming	
Luminous Flux	590 lm	Dimmable	No
Correlated Color Temperature (Nom)	3000 K	Control interface	-
Luminous Efficacy (rated) (Nom)	91 lm/W	Mechanical and Housing	
Color rendering index (CRI)	>90	Housing Material	Aluminum Alloy
Light source color	930 warm white	Optical cover material	Acrylate
Operating and Electrical		Housing Color	White
Input Voltage	200 to 240 V	Optical cover finish	Frosted
Line Frequency	50 to 60 Hz	Ingress protection code	IP20 [Finger-protected]
Power Consumption	5.4 6.6 W	Mech. impact protection code	IK03 [0.3 J]
Power Factor (Fraction)	0.9	Optical cover type	Acrylate

GreenSpace Accent Elbow GCGM

Net Weight (Piece)	0.345 kg
--------------------	----------

Approval and Application

CE mark	No
Ambient temperature range	-20 to +40 °C

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%

Product Data

Order product name	RS305B P6 930 PSU-E VWB
--------------------	-------------------------

Full product name	RS305B P6 930 PSU-E VWB
Full product code	872016952947299
Order code	52947299
Material Nr. (12NC)	911401563502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169529472
Numerator - Packs per outer box	36
EAN/UPC - Case	8720169540965

Dimensional drawing

